




## Evo5 Incremental Processor Full Automatic

The Evo 5 IP FA is the incremental version of the Vianord FA (Full Automatic) series in size 132 x 203 cm (52x80 inch). The FA Processor is the latest module to complete the Easy to Plate™ system. On top of all the features of a standard Processor, the FA version includes a fully automatic plate entrance section designed to receive plates directly for the Evo LED module or from a connecting bridge (the configuration depends on the LASER brand/model). Once a plate enters the processor, all operations are performed without any human intervention: pin bars are automatically taken and put in position from the pin bar charger; the plate is first punched, then clamped on the pin bar and carried throughout the whole process.


### PLATE ENTRANCE SECTION

- The side pin bar automatic charger stores up to 15 pin bars.
- The automatic punching system rolls up everytime the sensor identify an incoming plate. It punches the plate and goes back until the next one arrives.
- The clamping of the punched plate on the pin bar is taken care of automatically




### WASHOUT SECTION

- Digital washout with separate pre-wash section to prevent contamination
- of the main washout solvent with black layer
- 2 pre-wash brushes (oscillating and rotating)
- 10 washout brushes (oscillating and rotating)
- 1 top cleaning brush (oscillating and rotating)
- 1 wiping brush (oscillating and rotating)
- 2 back cleaning brushes (rotating)
- New volumetric pump and sensitive pressure sensor allow a higher precision solid content analyzer
- Automatic solvent replenishment system




- Fresh solvent consumption control over the machine life cycle and programmable over a time frame
- Fresh solvent flow regulation option on the touch screen
- Constant solvent temperature thanks to water circulation serpentine
- The new "3D Brush Motion" system with servo drive motors enables a soft mechanical start
- which results in less vibrations and a much more quiet 3D machine. It also provides a constant and repeatable washout speed; in fact, the new system, adjustable from the display, automatically synchronizes the brushes rotation and oscillation speed to the plate transfer speed; so that bristles hit the plate, thin or thick, always at the same speed




### OTHER FEATURES

- 30 x 30 cm rotating and tilting touch screen display
- Programmable automatic solvent warmup
- Automatic standby after the last plate processed
- Remote access (optional)
- Active component visualisation during the process
- Manual function to run the components separately
- Memorisation of the plate process parameters (up to 24 channels)







### Dimensions LxWxH

 5310 x 2200 x 1056 (panel 340) mm  
209.1 x 86.6 x 41.7 (panel 13.4) inches


### Power supply

 400V 3PH/N/PE 50/60Hz 7.5kW 12A  
230V 3PH/PE 50/60Hz 7.5kW 21A


### Plate thickness

 Up to 7 mm / 0.276 inch

### Solvent

 min solvent volume for operation: 134 lts  
max solvent volume for operation: 170 lts  
max tank volume: 190 lts  
solvent in & out pipes: 2 x 16 mm Ø

### Packaging dimensions

 processor: 3060 x 2260 x 1490 mm | 1.850 Kg  
plate exit: 2960 x 2260 x 1490 mm | 950 Kg

### Weight

2200 kg | 4850 pounds



### Maximum plate size

132 x 203 cm | 52 x 80 inches



### Compressed air supply

min. 7 bar



### Exhaust

1 x 140 mm Ø - 600 m<sup>3</sup>/h



### Remote monitoring

Optional



**Vianord**  
engineering  
[www.vianord.com](http://www.vianord.com)  
[info@vianord.com](mailto:info@vianord.com)

© 2015 Vianord. All rights reserved. The Vianord Logo®, Easy to Plate™ and Evo™ are registered trademarks or trademarks of Vianord Engineering SAS or its affiliates. All technical information set out herein is provided free of charge and is based on technical data, which Vianord believes to be reliable. It is intended for use by persons having skill, at their own discretion and risk. The handling precaution information contained herein is given with the understanding that those using it will satisfy themselves that their particular conditions of use present no health or safety hazards. Since conditions of product use are outside of our control we make no warranties express or implied in relation thereto and therefore cannot accept any liability in connection with any use of this information. Vianord Engineering SAS reserves the right to change the specifications of its products at any time. Nothing herein is to be taken as a license to operate under, or a recommendation to infringe any patents.